

BC-IM4

BC3

GR 1-2

GR 3-4

GR 5-6

GR 7-8

PGM

40 45 50 dB

36 55 60 65 MIC

28 70

25

PAD

P48

LINE

5 0 5

10 10

20 ±dB 20

PRE

PRE

2 3 4

1 5 6

0

PRE

PRE

2 3 4

1 5 6

0

PRE

CH-OUT

2 3 4

1 5 6

0

PRE

N-MINUS

C

L PAN R

3

CUE

POST

CUT

2 3 4

1 5 6

0

LEVEL

FILT

70 100 200

40 300 600 Hz

OFF

HPF

AUTOGAIN ON

10 5 0

15 5 10

20 15 20 dB

25 30

THR

.5 1

.3 3

.1 5ms

ATT

.5 1

.3 3

.1 5s

REL

25 20 dB

35 15

40 10

EXP

1.5 2 3

1.2 4 5

1.1 8

1 LIM

RAT

GR dB

1 3 5 10 20

4 0 4

9 9

15 15

HI

EXP-ON

1.5 7

.7 10

.3 15kHz

f

DYN

4 0 4

9 9

15 15

MID2

EQ

.25 1

.1 2

.06 3kHz

f

INS

4 0 4

9 9

15 15

±dB

LOW

PAN

C

L PAN R

START

PFL

CH-ON 24

PK

PS

FDR OPEN

